

FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions



FlexBlend Recessed RC340B
W60L60 MLO CPC








O FlexBlend Recessed-RC340B
W30L120 MLO VPC

Upgradable sensor




Dimensional drawing




FlexBlend Recessed

Dimensional drawing



FlexBlend Recessed

Dimensional drawing



Product details



Upgradable sensor

O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC




FlexBlend Recessed-
RC340B_MLO_DPP

FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C




FlexBlend Recessed-
RC340B_W60L60_CPC brackets

FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed

Product details



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP



O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC

FlexBlend Recessed

Product details



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend_RC340B_W30L120_U4
_DPP



Upgradable sensor



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Beam angle of light source	120 degree(s)
Optic type	Wide beam
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Mech. impact protection code	IK02
------------------------------	------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Maximum dim level	1%
-------------------	----

General Information

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B	Yes

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Temperature 650 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B	Yes
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Temperature 850 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B	Yes
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC340B	-
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s	Upgradable sensor slot with SNS210 sensor	RC342B	-
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	-	RC340B	Yes

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code	Service tag
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B	Yes
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Temperature 650 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B	Yes
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Temperature 850 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B	Yes
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B	Yes
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B	Yes
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B	Yes

Light Technical

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	4000 K	≥90	96 lm/W	3,600 lm
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	4000 K	≥90	95.5 lm/W	4,200 lm
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	4000 K	≥90	94.5 lm/W	4,200 lm
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	4000 K	≥90	88 lm/W	3,600 lm
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	86.5 lm/W	3,600 lm
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	4000 K	≥90	87.5 lm/W	4,200 lm
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	85.5 lm/W	4,200 lm
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	96 lm/W	3,600 lm
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	4000 K	≥90	94.5 lm/W	4,200 lm
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	4000 K	≥90	100 lm/W	2,800 lm
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	4000 K	≥90	97.5 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	4000 K	≥90	97.5 lm/W	3,600 lm
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	4000 K	≥90	140 lm/W	2,800 lm
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	4000 K	≥90	97 lm/W	3,600 lm
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	4000 K	≥90	140 lm/W	4,200 lm
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	4000 K	≥90	144 lm/W	3,600 lm
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	4000 K	≥90	124 lm/W	2,800 lm
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	4000 K	≥90	124 lm/W	3,600 lm
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	4000 K	≥90	125 lm/W	4,200 lm
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	4000 K	≥90	97.5 lm/W	3,600 lm
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	4000 K	≥90	100 lm/W	2,800 lm
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	4000 K	≥90	140 lm/W	2,800 lm
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	4000 K	≥90	97 lm/W	3,600 lm
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	4000 K	≥90	140 lm/W	4,200 lm
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	4000 K	≥90	124 lm/W	2,800 lm
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	4000 K	≥90	124 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	4000 K	≥90	125 lm/W	4,200 lm
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	4000 K	≥90	97.5 lm/W	3,600 lm
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	4000 K	≥90	144 lm/W	3,600 lm
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	3000 K	≥90	93.5 lm/W	3,600 lm
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	3000 K	≥90	93.5 lm/W	3,600 lm
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	3000 K	≥90	136 lm/W	3,600 lm
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	3000 K	≥90	136 lm/W	3,600 lm
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	4000 K	≥90	97.5 lm/W	3,600 lm
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	4000 K	≥90	97.5 lm/W	3,600 lm
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	4000 K	≥90	141 lm/W	3,600 lm
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	4000 K	≥90	141 lm/W	3,600 lm
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	4000 K	≥90	141 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	4000 K	≥90	140 lm/W	4,200 lm
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	4000 K	≥90	100 lm/W	2,800 lm
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	4000 K	≥90	140 lm/W	2,800 lm
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	4000 K	≥90	97.5 lm/W	3,600 lm
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	4000 K	≥90	141 lm/W	3,600 lm
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	4000 K	≥90	94.5 lm/W	4,200 lm
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	4000 K	≥90	140 lm/W	4,200 lm
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	4000 K	≥90	111 lm/W	3,600 lm
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	4000 K	≥90	109 lm/W	3,600 lm
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	4000 K	≥90	127 lm/W	4,200 lm
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	4000 K	≥90	125 lm/W	4,200 lm
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	4000 K	≥90	114 lm/W	4,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	4000 K	≥90	112 lm/W	4,200 lm
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	4000 K	≥90	125 lm/W	4,200 lm
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	4000 K	≥90	120 lm/W	3,600 lm
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	4000 K	≥90	124 lm/W	3,600 lm
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	4000 K	≥90	140 lm/W	4,200 lm
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	4000 K	≥90	141 lm/W	3,600 lm
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	4000 K	≥90	140 lm/W	4,200 lm
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	3000 K	≥90	136 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	4000 K	≥90	95.5 lm/W	4,200 lm
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	4000 K	≥90	94.5 lm/W	4,200 lm
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	4000 K	≥90	124 lm/W	3,600 lm
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	4000 K	≥90	124 lm/W	3,600 lm
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	4000 K	≥90	122 lm/W	3,600 lm
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	4000 K	≥90	141 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	4000 K	≥90	125 lm/W	4,200 lm
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	4000 K	≥90	124 lm/W	4,200 lm
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	3000 K	≥90	136 lm/W	4,200 lm
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	4000 K	≥90	140 lm/W	4,200 lm
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	4000 K	≥90	140 lm/W	4,200 lm
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	4000 K	≥90	144 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	4000 K	≥90	120 lm/W	3,600 lm
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	4000 K	≥90	88 lm/W	3,600 lm
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	4000 K	≥90	86.5 lm/W	3,600 lm
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	4000 K	≥90	124 lm/W	3,600 lm
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	4000 K	≥90	96 lm/W	3,600 lm
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	94.5 lm/W	4,200 lm
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	4000 K	≥90	94.5 lm/W	4,200 lm
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	95.5 lm/W	4,200 lm
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	4000 K	≥90	97.5 lm/W	3,600 lm
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	4000 K	≥90	142 lm/W	4,200 lm
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	3000 K	≥90	88.5 lm/W	4,200 lm
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	4000 K	≥90	94.5 lm/W	4,200 lm
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	4000 K	≥90	140 lm/W	4,200 lm
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	3000 K	≥90	136 lm/W	4,200 lm
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	4000 K	90	144 lm/W	3,600 lm
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO UO	4000 K	≥90	97.5 lm/W	3,600 lm
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS UO	4000 K	≥90	144 lm/W	3,600 lm
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	4000 K	≥90	96 lm/W	3,600 lm
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	4000 K	≥90	97.5 lm/W	3,600 lm
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	4000 K	≥90	100 lm/W	2,800 lm
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	4000 K	≥90	140 lm/W	2,800 lm
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	4000 K	≥90	144 lm/W	3,600 lm
910925867160	RC342B LED42S/940	4000 K	≥90	140 lm/W	4,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD W62L62 VPC PCS PIP				
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	4000 K	≥90	124 lm/W	2,800 lm
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	4000 K	≥90	124 lm/W	3,600 lm
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	4000 K	≥90	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	37.5 W
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	37 W
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	44 W
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	44.5 W
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	41 W
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	41.5 W
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	48 W
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	49 W
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	37.5 W
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	44.5 W
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	28 W
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	37 W
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	37 W
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	20 W
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	25 W
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	30 W
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	25 W
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	22.5 W
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	29 W
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	33.5 W
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	37 W
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	37 W
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	37 W
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	44.5 W
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	44.5 W
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	47.5 W
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	47.5 W

Order Code	Full Product Name	Power Consumption
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	30 W
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	30 W
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	31 W
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	28 W
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	20 W
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	25 W
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	30 W
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	22.5 W
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	29 W
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	33.5 W
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	37 W
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	25 W
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	38.5 W
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	38.5 W
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	26.5 W
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	26.5 W
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	37 W
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	37 W
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	25.5 W
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	25.5 W
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	25.5 W
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	30 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	28 W
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	20 W
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	37 W
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	25 W
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	44.5 W
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	30 W
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	32.5 W
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	33 W
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	33 W
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	33.5 W
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	37 W
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	37.5 W
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	33.5 W
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	30 W
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	29 W
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	30 W
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	24 W
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	24 W
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	47.5 W
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	44.5 W
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	30 W
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	31 W
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	37.5 W
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	44 W
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	44.5 W
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	30 W
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	31 W
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	29 W
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	37 W
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	29 W
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	29.5 W
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	25.5 W
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	30 W
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	30 W
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	33.5 W
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	34 W
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	31 W
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	30 W

Order Code	Full Product Name	Power Consumption
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	25 W
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	25 W
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	30 W
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	30 W
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	30 W
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	37 W
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	41 W
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	41.5 W
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	29 W
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	37.5 W
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	44.5 W
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	44.5 W
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	47.5 W
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	44.5 W
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	44 W
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	37 W
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	29.5 W
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	47.5 W
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	44.5 W
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	30 W
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	31 W
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	25 W
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	37 W
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	25 W
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	37 W
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	37 W
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	28 W
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	20 W
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	25 W
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	30 W
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	22.5 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	29 W

Order Code	Full Product Name	Power Consumption
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	33.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	No
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	No
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	No
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	No
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Yes
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Yes
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Yes
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Yes
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	No
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	Yes
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	Yes
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	Yes
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	Yes
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	Yes
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	Yes
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	Yes
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Yes
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Yes
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Yes
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Yes
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Yes
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Yes
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Yes
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Yes

Order Code	Full Product Name	Dimmable
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Yes
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	Yes
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	Yes
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	Yes
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	Yes
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	Yes
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	Yes
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	Yes
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	No
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	No
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	No
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	No
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	Yes
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	Yes
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	Yes
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	Yes
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	Yes
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	Yes
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	Yes
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	No
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	No
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	Yes
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	No
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	No
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	No
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	Yes
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	Yes
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	No
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	No
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes

FlexBlend Recessed

Order Code	Full Product Name	Dimmable
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	No
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	No
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	No
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	Yes
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	Yes
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	No
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes

Order Code	Full Product Name	Dimmable
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	Yes
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	Yes
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	Yes
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	Yes
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Yes
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Safety class I	IP20
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Safety class I	IP20
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Safety class I	IP20
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Safety class I	IP54
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Safety class I	IP20
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Safety class I	IP20
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	Safety class I	IP20
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	Safety class I	IP20
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	Safety class I	IP20
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	Safety class I	IP20
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	Safety class I	IP54

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	Safety class I	IP54
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	Safety class I	IP54
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Safety class III	IP20
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Safety class III	IP20/54
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Safety class I	IP20
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	Safety class I	IP20
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Safety class I	IP20/54
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	Safety class I	IP20/54
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Safety class I	IP20
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	Safety class I	IP20
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Safety class I	IP54
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Safety class I	IP54
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	Safety class I	IP54
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	Safety class I	IP54
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	Safety class I	IP20
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	Safety class I	IP54
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	Safety class I	IP20
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	Safety class I	IP54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	Safety class I	IP20
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	Safety class I	IP54
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Safety class I	IP54
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Safety class I	IP54
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Safety class I	IP54
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	Safety class I	IP54
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	Safety class I	IP54
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	Safety class I	IP54
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	Safety class I	IP20
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	Safety class I	IP20
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	Safety class I	IP54
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	Safety class I	IP54
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Safety class I	IP54
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	Safety class I	IP54
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Safety class I	IP54

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	Safety class I	IP54
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	Safety class I	IP54
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Safety class I	IP20
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Safety class I	IP20
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Safety class I	IP20
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	Safety class I	IP20
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	Safety class I	IP20
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Safety class I	IP20
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	Safety class I	IP20
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	Safety class I	IP20
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	Safety class I	IP54
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	Safety class I	IP54
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Safety class I	IP54
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Safety class III	IP20
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Safety class III	IP20/54
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Safety class I	IP20
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Safety class I	IP54
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Safety class I	IP54

FlexBlend Recessed

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Order Code	Full Product Name	Initial chromaticity
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3	910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	(0.38, 0.37) SDCM <3
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3	910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	0.43,0.39
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3	910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	0.43,0.39
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	(0.38, 0.37) SDCM <3	910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	0.43,0.39
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	0.43,0.39
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	0.38,0.37
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	0.38,0.37
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	0.38,0.37
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	0.38,0.37
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	(0.38, 0.37) SDCM <3	910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	0.38,0.37
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	(0.38, 0.37) SDCM <3	910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	0.38,0.37
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	(0.38, 0.37) SDCM <3	910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	0.38,0.37
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	(0.38, 0.37) SDCM <3	910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	0.38,0.37
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	0.38,0.37
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	0.38,0.37
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	0.38,0.37
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	(0.38, 0.37) SDCM <3	910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	0.38,0.37
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	(0.38, 0.37) SDCM <3	910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	(0.38, 0.37) SDCM <3	910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	(0.38, 0.37) SDCM <3	910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	(0.38, 0.37) SDCM <3	910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	(0.38, 0.37) SDCM <3	910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	(0.38, 0.37) SDCM <3	910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	(0.38, 0.37) SDCM <3
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	(0.38, 0.37) SDCM <3	910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	(0.38, 0.37) SDCM <3
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	(0.38, 0.37) SDCM <3	910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	(0.38, 0.37) SDCM <3
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	(0.43, 0.40) SDCM <3	910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	(0.38, 0.37) SDCM <3
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	(0.43, 0.40) SDCM <3	910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	0.38,0.37
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	(0.38, 0.37) SDCM <3	910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	0.38,0.37
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	(0.38, 0.37) SDCM <3	910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	0.38,0.37
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	(0.43, 0.40) SDCM <3	910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	(0.38, 0.37) SDCM <3	910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	(0.43, 0.40) SDCM <3
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	(0.38, 0.37) SDCM <3
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	(0.38, 0.37) SDCM <3
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	(0.38, 0.37) SDCM <3	910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	(0.43, 0.40) SDCM <3
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	(0.38, 0.37) SDCM <3			
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	(0.38, 0.37) SDCM <3			
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	(0.38, 0.37) SDCM <3			
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	(0.38, 0.37) SDCM <3			

FlexBlend Recessed

Order Code	Full Product Name	Initial chromaticity
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	(0.38, 0.37) SDCM <3
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	(0.43, 0.40) SDCM <3
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	(0.38, 0.37) SDCM <3
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	(0.38, 0.37) SDCM <3
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	(0.38, 0.37) SDCM <3
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	(0.43, 0.40) SDCM <3
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	(0.38, 0.37) SDCM <3
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	(0.38, 0.37) SDCM <3
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	(0.38, 0.37) SDCM <3
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	(0.38, 0.37) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	(0.38, 0.37) SDCM <3
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	(0.38, 0.37) SDCM <3
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	(0.38, 0.37) SDCM <3
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	(0.38, 0.37) SDCM <3
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	(0.43, 0.40) SDCM <3
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	(0.38, 0.37) SDCM <3
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	(0.38, 0.37) SDCM <3
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	(0.38, 0.37) SDCM <3
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	(0.43, 0.40) SDCM <3
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	(0.38, 0.37) SDCM <3
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	(0.38, 0.37) SDCM <3
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	(0.43, 0.40) SDCM <3
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	(0.38, 0.37) SDCM <3
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	(0.38, 0.37) SDCM <3
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	(0.38, 0.37) SDCM <3
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	(0.38, 0.37) SDCM <3
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	(0.38, 0.37) SDCM <3
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	(0.38, 0.37) SDCM <3
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	(0.38, 0.37) SDCM <3
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	(0.38, 0.37) SDCM <3
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	(0.38, 0.37) SDCM <3
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	(0.38, 0.37) SDCM <3

Over Time Performance (IEC Compliant)

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	0.01 %
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	0.01 %
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	0.01 %
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	0.01 %
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	0.01 %
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	0.01 %
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	-
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	-
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	-
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	-
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	-
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	-
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	-
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	-
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	-
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	-
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	0.01 %
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	0.01 %
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	0.01 %
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	0.01 %
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	0.01 %
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	0.01 %
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	0.01 %
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	0.01 %
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	0.01 %
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	0.01 %
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	-
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	-
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	-
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	-
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	-
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	-
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	-
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	-
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	-
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	-
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	-
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	-
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	-
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	-
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	-
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	-
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	-
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	-
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	-
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	-
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	-
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	-
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	-
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	-
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	0.01 %
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	0.01 %
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	0.01 %
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	0.01 %
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	0.01 %
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	0.01 %
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	0.01 %
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	-
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	-
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	-
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	0.01 %
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	0.01 %
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	0.01 %
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	0.01 %
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	0.01 %
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	0.01 %
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	0.01 %
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	-
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	0.01 %
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	0.01 %
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	0.01 %
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	0.01 %
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	0.01 %
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	0.01 %
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	0.01 %
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	0.01 %
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	0.01 %
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	0.01 %
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	0.01 %
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	0.01 %
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	0.01 %
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	0.01 %
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	0.01 %
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	0.01 %
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	0.01 %
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	0.01 %
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	0.01 %

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	0.01 %
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	0.01 %
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	0.01 %
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	0.01 %
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	0.01 %
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	0.01 %
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	0.01 %
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	0.01 %
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	0.01 %
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	-
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	-
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	-
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	0.01 %
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	0.01 %
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	-
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	-
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	-
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	-
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	-
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	-
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	-

Application Conditions

Order Code	Full Product Name	Suitable for random switching
910925867015	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Yes
910925867016	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
910925867017	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Yes
910925867018	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
910925867019	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Yes
910925867020	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867021	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Yes
910925867022	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867024	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
910925867026	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
910925867149	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Yes
910925867150	RC342B LED36S/940 PSD W15L125 VPC MLO	Yes
910925867153	RC342B LED36S/940 PSD W17L125 PCV MLO	Yes
910925867164	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Yes
910925867165	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
910925867166	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
910925867169	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes
910925867180	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
910925867181	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
910925867182	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
910925866979	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
910925866982	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Yes
910925866983	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
910925867030	RC340B LED42S/940 PSD W30L120 VPC MLO W	Yes
910925867031	RC340B LED42S/940 PSD W30L120 CPC MLO W	Yes
910925867032	RC340B LED42S/930 PSD W30L120 VPC MLO W	Yes
910925867033	RC340B LED42S/930 PSD W30L120 CPC MLO W	Yes
910925867038	RC340B LED42S/940 PSD W30L120 VPC PCS W	Yes
910925867039	RC340B LED42S/940 PSD W30L120 CPC PCS W	Yes
910925867042	RC340B LED42S/930 PSD W30L120 VPC PCS W	Yes
910925867147	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes

Order Code	Full Product Name	Suitable for random switching
910925867161	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
910925867162	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
910925867163	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
910925867177	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
910925867178	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
910925867179	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes
910925867222	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes (relates to presence/movement detection and daylight harvesting)
910925867225	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes (relates to presence/movement detection and daylight harvesting)
910925868910	RC340B LED36S/930 SRD W60L60 VPC MLO U4	No
910925868911	RC340B LED36S/930 SRD W60L60 VPC MLO U4	No
910925868912	RC340B LED36S/930 SRD W60L60 VPC PCS U4	No
910925868913	RC340B LED36S/930 SRD W60L60 VPC PCS U4	No
910925868914	RC340B LED36S/940 SRD W60L60 VPC MLO U4	No
910925868915	RC340B LED36S/940 SRD W60L60 VPC MLO U4	No
910925868916	RC340B LED36S/940 SRD W60L60 VPC PCS U4	No
910925868917	RC340B LED36S/940 SRD W60L60 VPC PCS U4	No
910925868918	RC340B LED36S/940 SRD W60L60 VPC PCS U4	No
910925868920	RC340B LED42S/940 SRD W60L60 VPC PCS U4	No
910925868921	RC342B LED28S/940 SRD W62L62 VPC MLO U4	No
910925868922	RC342B LED28S/940 SRD W62L62 VPC PCS U4	No
910925868924	RC342B LED36S/940 SRD W62L62 VPC MLO U4	No

FlexBlend Recessed

Order Code	Full Product Name	Suitable for random switching
910925868925	RC342B LED36S/940 SRD W62L62 VPC PCS U4	No
910925868927	RC342B LED42S/940 SRD W62L62 VPC MLO U4	No
910925868928	RC342B LED42S/940 SRD W62L62 VPC PCS U4	No
910925866986	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Yes
910925866987	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
910925867001	RC340B LED42S/940 PSU W60L60 VPC O PIP	Yes
910925867002	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
910925867006	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Yes
910925867007	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
910925867012	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
910925867061	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Yes
910925867062	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
910925868919	RC340B LED42S/940 SRD W30L120 VPC PCS U4	No
910925868923	RC342B LED36S/940 SRD W31L125 VPC PCS U4	No
910925868926	RC342B LED42S/940 SRD W31L125 VPC PCS U4	No
910925866969	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925867023	RC340B LED42S/930 PSD W60L60 CPC MLO W	Yes
910925867028	RC340B LED42S/940 PSD W60L60 CPC MLO W	Yes
910925867036	RC340B LED42S/940 PSD W60L60 CPC PCS W	Yes
910925867040	RC340B LED42S/930 PSD W60L60 CPC PCS W	Yes
910925867046	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Yes
910925867047	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Yes
910925867048	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
910925867167	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
910925867068	RC340B LED42S/930 PSD W30L120 CPC PCS W	Yes
910925866967	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
910925866972	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
910925866973	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866977	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
910925866990	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Yes
910925866991	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
910925866997	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
910925867003	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Yes
910925867004	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
910925867008	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Yes
910925867009	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
910925867034	RC340B LED42S/930 PSD W60L60 VPC PCS W	Yes
910925867035	RC340B LED42S/940 PSD W60L60 VPC PCS W	Yes
910925867044	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Yes
910925867045	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
910925867049	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Yes
910925867050	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes
910925867065	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
910925867066	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
910925866966	RC340B LED36S/940 PSU W60L60 VPC O PIP	Yes

Order Code	Full Product Name	Suitable for random switching
910925866980	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Yes
910925866988	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Yes
910925866989	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
910925866993	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
910925866995	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
910925866999	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
910925867010	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
910925867013	RC340B LED42S/930 PSD W60L60 VPC MLO W	Yes
910925867027	RC340B LED42S/940 PSD W60L60 VPC MLO W	Yes
910925867043	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Yes
910925867063	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
910925867064	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
910925866970	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
910925867014	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
910925867025	RC340B LED42S/930 PSD W60L60 PCV MLO W	Yes
910925867029	RC340B LED42S/940 PSD W60L60 PCV MLO W	Yes
910925867037	RC340B LED42S/940 PSD W60L60 PCV PCS W	Yes
910925867041	RC340B LED42S/930 PSD W60L60 PCV PCS W	Yes
910925867168	RC340B LED36S/940 PSD W60L60 PCV PCS PIP	Yes
910925867221	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes (relates to presence/movement detection and daylight harvesting)
910925867224	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes (relates to presence/movement detection and daylight harvesting)
910925866968	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
910925866978	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
910925866981	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
910925867145	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
910925867158	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
910925867159	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
910925867160	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
910925867174	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
910925867175	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
910925867176	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

FlexBlend Recessed

