



GreenVision Xceed Gen2

BRP383 LED280/NW 200W 220-240V DM PSR

GreenVision Xceed Gen2, 28000 lm, 200 W, 740 neutral white, Analog, Safety class I

Sustainability, citizen well being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving this goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads & streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, highways and rural areas – our luminaires provide the optimal light for all application areas. And, GreenVision Xceed Gen2 is ready to be connected and work with smart city ecosystem. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	140 lm/W
Driver included	Yes	Color rendering index (CRI)	>70
CE mark	CE mark	Light source color	740 neutral white
Warranty period	3 years	Optical cover type	Polycarbonate micro lens optic
Flammability mark	For mounting on normally flammable surfaces	Operating and Electrical	
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	28,000 lm	Line Frequency	50 or 60 Hz
Correlated Color Temperature (Nom)	4000 K	Power Consumption	200 W
		Power Factor (Fraction)	0.9

GreenVision Xceed Gen2

Connection	-
Cable	-

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Gray
Overall length	736 mm
Overall width	314 mm
Overall height	138 mm
Effective projected area	0.23 m ²
Dimensions (Height x Width x Depth)	138 x 314 x 736 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM < 5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	100,000 hour(s)
---------------------------	-----------------


Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BRP383 LED280/NW 200W 220-240V DM PSR
Full product name	BRP383 LED280/NW 200W 220-240V DM PSR
Full product code	872016952045500
Order code	911401874898
Material Nr. (12NC)	911401874898
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169520455
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169520455

Dimensional drawing



GreenVision Xceed Gen2

