



CorePro LEDlinear MV



CoreProLED linearD 17.5-150W R7S 118 840

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its ‘light all around’ design delivers light just like a halogen lamp. Within the range you can choose dimmable products which have deep dimming function that enables a cozy ambience when using a dimmable fixture.

Product data

General Information	
Cap-Base	R7s
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,460 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	17.5 W
Lamp Current (Nom)	90 mA
Wattage Equivalent	150 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	102 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Shape	Linear
Approval and Application	
Energy Efficiency Class	D
Suitable For Accent Lighting	No

CorePro LEDlinear MV

Energy Consumption kWh/1000 h	18 kWh
EPREL Registration Number	397598
EyeComfort	Yes

Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

Product Data


Order product name	CoreProLED linearD 17.5-150W R7S 118 840
Full product name	CoreProLED linearD 17.5-150W R7S 118 840

Full product code	871869964675200
Order code	929002016702
Material Nr. (12NC)	929002016702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699646752
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699646769


Dimensional drawing

Product	D	C
CoreProLED linearD 17.5-150W R7S 118 840	42 mm	118 mm

Photometric data




Spectral Power Distribution Colour - CoreProLED linearD 17.5-150W R7S 118 840



Light Distribution Diagram - CoreProLED linearD 17.5-150W R7S 118 840


CorePro LEDlinear MV

Photometric data




General uniform lighting - CoreProLED linearD 17.5-150W R7S 118 840

Lifetime



Lumen Maintenance Diagram - CoreProLED linearD 17.5-150W R7S 118 840



Life Expectancy Diagram - CoreProLED linearD 17.5-150W R7S 118 840

