



Actinic BL TL(-K) / TL-D(-K)

Actinic BL TL-D 15W/10 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		UV Depreciation at 8000 h	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		20 %
Life to 50% Failures (Nom)	8,000 hour(s)	Operating and Electrical	
Useful Life (Nom)	9,000 hour(s)	Power Consumption	15 W
		Lamp Current (Nom)	0.34 A
		Voltage (Nom)	55 V
Light Technical		Mechanical and Housing	
Color Code	10	Bulb Shape	T26
Color Designation	Actinic	Approval and Application	
Chromaticity Coordinate X (Nom)	222	Mercury (Hg) Content (Nom)	5.0 mg
Chromaticity Coordinate Y (Nom)	210		
UV Depreciation at 2000 h	10 %		
UV Depreciation at 5000 h	15 %		


Actinic BL TL(-K) / TL-D(-K)

UV	
UV-A Radiation 100Hr (IEC)	3.9 W
Product Data	
Order product name	Actinic BL TL-D 15W/10 1SL/25
Full product name	Actinic BL TL-D 15W/10 1SL/25
Full product code	871150071093240
Order code	928024801029


Material Nr. (12NC)	928024801029
Numerator - Quantity Per Pack	1
Net Weight (Piece)	56.570 g
EAN/UPC - Product/Case	8711500710932
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500710949

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm



Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 15W/10 1SL/25

