



Magnetic Sys

Mag L Spotlight 5.5W 530lm 30K 24D

Magnetic Sys, 5.5 W, 530 lm, 3000 K, Beam angle 24°, Black

Magnetic Sys offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance. Also an ideal solution for easy installation and DIY design friendly.

Product data

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	No
Switching Cycle	12,500
Lighting Technology	LED
Warranty period	1 years

Light Technical	
Luminous Flux	530 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	96.00 lm/W
Color rendering index (CRI)	90
Light source color	930 warm white
Optic type	Beam angle 24°
Luminaire light beam spread	24°

Operating and Electrical	
Input Voltage	24 V
Line Frequency	- Hz
Input Frequency	- Hz

Power Consumption	5.5 W
Power Factor (Fraction)	-
Connection	Connection unit 2-pole
Suitable for random switching	No
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Metal-Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	Black
Optical cover finish	Textured
Overall length	228 mm
Overall width	22 mm

Magnetic Sys

Overall height	43 mm
Dimensions (Height x Width x Depth)	43 x 22 x 228 mm
Net weight	0.17 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.170 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	3 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	((, 0.4336, 0.4050) <5

Power consumption tolerance	+/-10%
-----------------------------	--------


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1.5 %
Median useful life L70B50	25,000 hour(s)



Product Data

Order product name	Mag L Spotlight 5.5W 530lm 30K 24D
Full product name	Mag L Spotlight 5.5W 530lm 30K 24D
Full product code	692234195475700
Order code	929003207210
Material Nr. (12NC)	929003207210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341954757
Numerator - Packs per outer box	20
EAN/UPC - Case	6922341954764

Dimensional drawing



Photometric data



General uniform lighting - Mag L Spotlight 5.5W 530lm 30K 24D

Light Distribution Diagram - Mag L Spotlight 5.5W 530lm 30K 24D

