



# Magnetic Sys

## Mag Ad L Spotlight 5.5W 530lm 30K 24D

Magnetic Sys, 5.5 W, 530 lm, 3000 K, Beam angle 24°, Black

Magnetic Sys offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance. Also an ideal solution for easy installation and DIY design friendly.

### Product data

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	No
Switching Cycle	12,500
Lighting Technology	LED
Warranty period	1 years

Light Technical	
Luminous Flux	530 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	96.00 lm/W
Color rendering index (CRI)	90
Light source color	930 warm white
Optic type	Beam angle 24°
Luminaire light beam spread	24°

Operating and Electrical	
Input Voltage	48 V
Line Frequency	- Hz
Input Frequency	- Hz

Power Consumption	5.5 W
Power Factor (Fraction)	-
Connection	Connection unit 2-pole
Suitable for random switching	No
Protection class IEC	Safety class III

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Metal-Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	Black
Optical cover finish	Textured
Overall length	235 mm
Overall width	22 mm

# Magnetic Sys

Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 22 x 235 mm
Net weight	0.28 kg
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	0.280 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
EU RoHS compliant	Yes
Warranty	3 year(s)
EyeComfort	Yes
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	( ( , 0.4336, 0.4050 ) <5

Power consumption tolerance	+/-10%
-----------------------------	--------


## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1.5 %
Median useful life L70B50	25,000 hour(s)


## Product Data

Order product name	Mag Ad L Spotlight 5.5W 530lm 30K 24D
Full product name	Mag Ad L Spotlight 5.5W 530lm 30K 24D
Full product code	692234195483200
Order code	929003207610
Material Nr. (12NC)	929003207610
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341954832
Numerator - Packs per outer box	10
EAN/UPC - Case	6922341954849

## Dimensional drawing



## Photometric data



Light Distribution Diagram - Mag Ad L Spotlight 5.5W 530lm 30K 24D

General uniform lighting - Mag Ad L Spotlight 5.5W 530lm 30K 24D

