



# Pacific LED Gen5 Value

## WT475C 72S/840 PSU WB TW1 L1200

Pacific LED gen5 Value, 840 neutral white, Power supply unit (On/Off), Wide beam, Push-in connector 5-pole

Pacific LED Gen5 Value is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact, and reliable luminaire, with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED Gen5 Value can perfectly withstand the harsh conditions of automotive, food and heavy industries. But this waterproof lighting also performs well in parking garages and warehouses. With multiple optics and a broad range of light outputs. Pacific LED Gen5 Value luminaires provide superior, artefact-free light quality and homogeneous light. This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. These luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also due to their energy efficiency and ease of maintenance – with the minimum of disruption to operations in demanding applications. Discover Pacific LED Gen5 Value. Robust luminaires with optimal performance for waterproof lighting.

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof seal and IP66 rating
- Do not install the luminaire in locations where it will be exposed to direct sunlight

### Product data

# Pacific LED Gen5 Value

General Information	
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Product family code	WT475C [Pacific LED gen5 Value]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical	
Luminous Flux	7,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	93° x 93°
Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22.4 A
Inrush time	0.326 ms
Power Consumption	54 W
Power Factor (Fraction)	0.98
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	34

Temperature	
Ambient temperature range	-25 to +45 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	-

Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,278 mm
Overall width	96 mm
Overall height	68 mm
Dimensions (Height x Width x Depth)	68 x 96 x 1278 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0 m

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data	
Order product name	WT475C 72S/840 PSU WB TW1 L1200
Full product name	WT475C 72S/840 PSU WB TW1 L1200
Full product code	871951462337800
Order code	910925868272
Material Nr. (12NC)	910925868272
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514623378
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514623378

# Pacific LED Gen5 Value

## Dimensional drawing

