



Essential Smartbright Projector Gen 2

ST033T LED17/840 20W 220-240V I WB BK GM

Essential Smartbright Projector Gen 2, 20 W, 840 neutral white, Finger-protected

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver, and choice in 24 or 36 degree beam angle makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to it's predecessor, it is not only cost effective, but also a more sleek and lighter product design. The product family includes 1M and 2M Track in Black and white color with I and L connector to support various applications.

Product data

General Information		Light source color	
Light source engine type	LED		840 neutral white
CE mark	-	Optical cover type	Fashion proof optic beam angle 36°
Flammability mark	-	Operating and Electrical	
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	1,700 lm	Line Frequency	50 or 60 Hz
Correlated Color Temperature (Nom)	4000 K	Inrush current	15 A
Luminous Efficacy (rated) (Nom)	85 lm/W	Power Consumption	20 W
Color rendering index (CRI)	>80	Power Factor (Fraction)	0.5

