



# Classic filament LED candles and lusters

## LEDClassic 4.5W A15 E27 850 CL ND 1PF/10

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data


General Information		Power Consumption	
Cap-Base	E27	Lamp Current (Nom)	75 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	850 [CCT of 5000K]	T-Case Maximum (Nom)	50 °C
Luminous Flux	500 lm		
Color Designation	Daylight	Controls and Dimming	
Correlated Color Temperature (Nom)	5000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	111.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A15
Operating and Electrical		Product Data	
Line Frequency	60 Hz	Order product name	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10
Input Frequency	60 Hz		

# Classic filament LED candles and lusters

Full product name	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10
Order code	929003068042
Material Nr. (12NC)	929003068042
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677571931



Numerator - Packs per outer box	10
EAN/UPC - Case	50046677571936

## Dimensional drawing




Product	D	C
LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	48 mm	89 mm

## Photometric data



Spectral Power Distribution Colour - LEDClassic 4.5W A15 E27 850 CL ND 1PF/10

Light Distribution Diagram - LEDClassic 4.5W A15 E27 850 CL ND 1PF/10



General uniform lighting - LEDClassic 4.5W A15 E27 850 CL ND 1PF/10

# Classic filament LED candles and lusters

## Lifetime



Life Expectancy Diagram - LEDClassic 4.5W A15 E27 850 CL ND 1PF/10

Lumen Maintenance Diagram - LEDClassic 4.5W A15 E27 850 CL ND 1PF/10

