



# Classic filament LED candles and lusters

## LEDClassic 4.5W B11 E12 850 CL ND 3CT/10

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	111.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz


Power Consumption	4.5 W
Lamp Current (Nom)	75 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B11
Product Data	
Order product name	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10

# Classic filament LED candles and lusters

Full product name	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10
Order code	929003068448
Material Nr. (12NC)	929003068448
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677572068



Numerator - Packs per outer box	10
EAN/UPC - Case	50046677572063

## Dimensional drawing




Product	D	C
LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	35 mm	99 mm

## Photometric data



Spectral Power Distribution Colour - LEDClassic 4.5W B11 E12 850 CL ND 3CT/10


Light Distribution Diagram - LEDClassic 4.5W B11 E12 850 CL ND 3CT/10



General Uniform Lighting - LEDClassic 4.5W B11 E12 850 CL ND 3CT/10

# Classic filament LED candles and lusters

## Lifetime



Life Expectancy Diagram - LEDClassic 4.5W B11 E12 850 CL ND 3CT/10

Lumen Maintenance Diagram - LEDClassic 4.5W B11 E12 850 CL ND 3CT/10

